


BI7-Q08-LIU-0.2-RS4.4T Inductive Sensor – With Analog Output




Technical data

Type	BI7-Q08-LIU-0.2-RS4.4T
ID no.	1534692
Measuring range	1...4 mm
Mounting conditions	Flush
Secured operating distance	$\leq (0.81 \times S_n)$ mm
Correction factors	St37 = 1; Al = 0.3; stainless steel = 0.7; Ms = 0.4
Repeatability	$\leq 1 \%$ of measuring range A - B
	0.5 %, after warm-up 0.5 h
Reproducibility	$\leq 30 \mu\text{m}$
	$\leq 15 \mu\text{m}$, after a warm-up time of 0.5 h
Linearity deviation	$\leq 5 \%$
Temperature drift	$\leq \pm 0.06 \%$ / K
Ambient temperature	-25...+70 °C
Operating voltage	15...30 VDC
Residual ripple	$\leq 10 \%$ U_{ss}
No-load current	$\leq 8 \text{ mA}$
Isolation test voltage	$\leq 0.5 \text{ kV}$
Short-circuit protection	yes
Wire breakage/Reverse polarity protection	no / Complete
Output function	4-wire, Analog output
Voltage output	0...10 V
Current output	0...20 mA
Load resistance voltage output	$\geq 4.7 \text{ k}\Omega$
Load resistance, current output	$\leq 0.4 \text{ k}\Omega$

Features

- Rectangular, height 8 mm
- Active face on top
- Metal, Zamak, nickel-plated
- 4-wire, 15...30 VDC
- Analog output
- 0...10 V and 0...20 mA
- Cable with connector, M12 × 1

Wiring diagram




Functional principle

Inductive TURCK sensors with analog output accomplish simple control tasks. They provide a current, voltage or frequency signal proportional to the target's distance. The output signal is linear to the distance of the target over the entire sensing range.

Technical data

Measuring sequence frequency	200 Hz
Design	Rectangular, Q08
Dimensions	32 x 20 x 8 mm
Housing material	Metal, Zamak, Nickel-plated
Active area material	Plastic, PP, yellow
Electrical connection	Connector, M12 × 1
Cable quality	Ø 3 mm, Gray, LifY-11Y, PUR, 0.2 m
Core cross-section	4 x 0.14 mm ²
Vibration resistance	55 Hz (1 mm)
Shock resistance	30 g (11 ms)
Protection class	IP68
MTTF	751 years acc. to SN 29500 (Ed. 99) 40 °C



Mounting instructions

Mounting instructions/Description	
	Distance D 40 mm
	Distance W 24 mm
	Distance G 48 mm
	Width active area B 20 mm