for 4 POF or MOST® 31 contacts (DIN 41626-3)



The modular inserts must be installed in suitable frames which are then mounted in traditional enclosures or in COB panel support.

Single-sized modular units may be directly mounted inside MIXO ONE enclosures.

page:

frames for modular units 316 - 317

MIXO ONE enclosures 369 modular units. crimp connections



POF / MOST crimp contacts



description	part No.	part No.	
without contacts (to be ordered separately)			
female inserts for female contacts 1)	CX 04 LF		
male inserts for male contacts 1)	CX 04 LM		
female contacts POF 2) 1,0 mm		CX PLF	
male contacts POF 2) 1,0 mm		CX PLM	
female contacts MOST _® ³⁾ 1/1,5 mm		CX MLF	
male contacts MOST _® ³⁾ 1/1,5 mm		CX MLM	

2) POF = POLYMER OPTICAL FIBRE

3) MOST_® = MEDIA ORIENTED SYSTEM TRANSPORT

MOST_® = is a registered trade mark of Microchip Technology Inc.


- c Sus (UL for USA and Canada), 👀 🗫 VERITAS [certified 1)




- insulation resistance: ≥ 1 GΩ
- ambient temperature limit: -40 $^{\circ}\text{C}$... +85 $^{\circ}\text{C}$
- inserts made of self-extinguishing thermoplastic
- resin UL 94V-0
- mechanical life: ≥ 500 cycles
- contact resistance: ≤ 30 mΩ
- for crimp contacts CI series use:
- CIPZ D crimping tool
- CITP D turret head
- max external diameter: 2,2 mm (POF)
 - 2,3 mm (MOST)
- polymer fibre diameter: 1,0 mm (POF)
 - 1/1,5 mm (MOST)
- attenuation: < 2.5 dB
- to crimp contacts CX PLF / PLM and CX MLF / MLM please use tool CLPZ R (see the crimping tool section on page 730)

We recommend to use CLASS enclosures with two levers or V-TYPE enclosures (with one or two levers) that provides a higher coupling depth due to the higher locking force they produce. We further suggest the use of code pins CRF CX / CRM CX.

CX 04 LF / LM










contacts side (front view)

side with reference arrow A







- 1 frame slot



cable stripping for fibre optic



male contact



female contact